SLM-1ER Slit Lamp

Simple but not crude, all functions, flexible operate, comfortable check

- OHas 10X and 16X two types eyepiece, with deflector rod, has 10X, 16X and 25.6X three magnification
- Maximum 14mm spot checks greater extent of disease
- ©21.5mm high eye point more comfortable to check
- OBuilt-in five filters(Unfiltered, heat absorption, grey, cobalt blue, red free), freely selected according to requirement
- OInternational standard accessories interface, you can install any model of anterior segment laser adapter and Goldman tenonometer



Technical Specification	
Model	SLM-1ER
Microscope Type	Converging
Magnification Change Way	Deflector Rod
Eyepiece Magnification	10X 16X
Total Magnifications	10X 16X 25X
Diopter Adjustment	-6D~+6D
Illumination	Three Steps (Stepless Optional)
Slit Width	(0-14MM Continuous)
Slit Height	(1-14MM Continuous)
Slit Angle	0° − 180° Adjustable
Slit Inclination Angle	5° 10° 15° 20°
Light Spot Diameter	0.2mm,1mm,2mm,5mm,10mm,14mm
Filter	Heat Absorption; Grey; Redfree; Cobalt Blue
Fixation	Red LED
Electrical	
Illumination Bulb	German OSRAM Halogen Tungsten Lamp LED lamp(optional)
Input Voltage	110V/220V (±10%)
Input Power	60VA
Diffuse Lens	Yes
Preset Lens	Yes
Laser Interface	Optional
Applanation Tonometer Interface	Yes
Base movement:	
X:	100mm±3
Y:	75mm±3
Z:	30mn±3

3